



# Low Cost Handheld Thermometers **OMEGATEMP™**

- ✓ Lightweight Design
- ✓ Pocket Clip and Magnet Hanger
- ✓ MAX/DATA HOLD Function



HH67  
**£37**



HH67 shown smaller than actual size

## HH67 Semiconductor Thermometer with Probe Attached

### Specifications

#### Temperature:

**Range:** -50 to 150°C (-58 to 302°F)

**Resolution:** 0.1°C (1°F)

#### Accuracy:

- ±3.0°C from -50 to 0°C
- ±1.5°C from 0 to 100°C
- ±3.0°C from 100 to 150°C;
- ±6.0°F from -58 to 32°F
- ±3.0°F from 32 to 212°F
- ±6.0°F from 212 to 302°F

**Sensor:** Semiconductor, silicon diode type

**Dimensions:** 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

**Weight:** Approx. 78 g (2.7 oz.) including battery

**Probe:** Brass with conformal coating

**Probe Diameter:** 3.2 mm (1/8") with pointed tip

**Probe Length:** 130 mm (5.1")

**Display:** 3 1/2 digit liquid crystal display (LCD)

**Low Battery Indication:** The "EOL" is displayed when the battery voltage drops below the operating level

**Measurement Rate:** 2.5 times/second

**Operating Environment:** 0 to 50°C (32 to 122°F) <70% R.H.

**Storage Environment:** -20°C to 60°C (-4 to 140°F), 0 to 80% R.H. with battery removed from meter

**Accuracy:** Stated accuracy at 23°C ± 5°C (73°F ± 9°F), <75% R.H.

**Battery:** 1.5V x 3pcs AAA size, included

**Battery Life:** 300 hours, typical use

- ✓ Auto Power Off Function Can Be Disabled
- ✓ Battery Life 300 Hrs. Typical Use
- ✓ °C/°F Switchable



HH68K  
**£43.50**



HH68K shown smaller than actual size

## HH68K Type K Thermometer with Probe Attached

### Specifications

#### Temperature:

**Range:** -100 to 850°C (-148 to 1562°F)

type K (CHROMEGA™-ALOMEGA™)

**Resolution:** 1°C or 1°F, 0.1°C or 0.1°F

**Accuracy (does not include probe):** 18 to 28°C (64 to 82°F) ambient ±(0.3% rdg + 1°C) on °C ranges ±(0.3% rdg + 2°F) on °F ranges

#### Resolution

Resolution	Range
0.1°C	-59.9 to 199.9°C
1°C	-100 to -60°C; 200 to 850°C
0.1°F	-59.9 to 199.9°F
1°F	-148 to -60°F; 200 to 1562°F

**Dimensions:** 160 H x 48 W x 24 mm D (6.3 x 1.9 x .94")

**Weight:** Approx. 80 g (2.8 oz.) including battery

**Probe:** Stainless steel

**Probe Diameter:** 3.2 mm (1/8") with pointed tip

**Probe Length:** 132 (5.2")

**Display:** 3 1/2 digit liquid crystal display (LCD)

**Low Battery Indication:** The "EOL" is displayed when the battery voltage drops below the operating level

**Measurement Rate:** 2.5 times/second

**Operating Environment:** 0 to 50°C (32 to 122°F) <70% R.H.

**Storage Environment:** -20 to 60°C (-4 to 140°F), 0 to 80% R.H. with battery removed from meter

**Accuracy:** Stated accuracy at 23°C ± 5°C (73°F ± 9°F), <75% R.H.

**Battery:** 1.5V x 3pcs AAA size, included

**Battery Life:** 300 hours, typical use

### ALL MODELS AVAILABLE FOR FAST DELIVERY!

#### To Order (Specify Model Number)

Model No.	Price	Description
HH67	£37.00	Semiconductor thermometer with probe attached
HH68K	43.50	Type K thermometer with probe attached
SC67	6.70	Soft carrying case

Comes with complete operator's manual, magnet hanger, and batteries.

Ordering Example: HH68K, type K thermometer with probe attached, £43.50.

#### Applications

- Greenhouses
- Office Environment
- Department Stores
- Labs
- Weather Monitoring
- Art Galleries
- Museums
- Workshops
- Environmental Studies

