

# Pocket Testers

## For Temperature and Relative Humidity

PTH-1XA

£35



PTH-1XA, £35, shown smaller than actual size.

- ✓ Simultaneous Display of Temperature and Humidity
- ✓ Auto Power-Off (20 min)
- ✓ Memory (Min/Max)
- ✓ °C/°F Switch

- ✓ On/Off Switch
- ✓ Belt or Pocket Clip
- ✓ Batteries Included
- ✓ Pocket Sized
- ✓ Reset Switch
- ✓ Hold Switch

### Specifications

**Colour:** Dark grey  
**Power Supply:** One button cell included (CR2032)  
**Humidity Range:** 5 to 95% RH  
**Accuracy:** 10 to 90% RH  $\pm 3\%$ , all other ranges  $\pm 5\%$   
**Temperature Range:**  
 $\pm 1^\circ\text{C}$  ( $\pm 2^\circ\text{F}$ ): 0 to  $40^\circ\text{C}$  (32 to  $104^\circ\text{F}$ )  
 $\pm 1^\circ\text{C}$  ( $\pm 2^\circ\text{F}$ ): 0 to  $40^\circ\text{C}$  (32 to  $104^\circ\text{F}$ )  
**Response Time:** 80 s typical

RH-122

£20



RH-122, £20, shown smaller than actual size.

- ✓ Simultaneous Display of Temperature and Humidity
- ✓ Auto Power-Off (20 min)
- ✓ Memory (Min/Max)

- ✓ °C/°F Switch
- ✓ On/Off Switch
- ✓ Pocket Clip
- ✓ Batteries Included
- ✓ Pocket Sized

### Specifications

**Colour:** Black  
**Power Supply:** One button cell included (LR44)  
**Humidity Range:** 20 to 90% RH  
**Accuracy:**  $\pm 5\%$   
**Temperature Range:**  $-10$  to  $50^\circ\text{C}$  (14 to  $122^\circ\text{F}$ )  
**Accuracy:**  $\pm 1^\circ\text{C}$  ( $\pm 1.8^\circ\text{F}$ )  
**Response Time:** 80 s typical

RH-1X

£26



RH-1X, £26, shown smaller than actual size.

- ✓ Simultaneous Display of Temperature and Humidity
- ✓ Auto Power-Off (10 min)
- ✓ Memory (Min/Max)
- ✓ °C/°F Switch
- ✓ Belt or Pocket Clip
- ✓ Pocket Sized
- ✓ Reset Switch

### Specifications

**Colour:** Silver and Black  
**Power Supply:** "AAA" battery (included)

**Measurement Range:** 5 to 95% RH,  $-20$  to  $60^\circ\text{C}$  ( $-4$  to  $140^\circ\text{F}$ )  
**Humidity Accuracy:** 30 to 80% RH  $\pm 3\%$ , all other ranges  $\pm 5\%$   
**Temperature Accuracy:**  $\pm 1^\circ\text{C}$  ( $\pm 2^\circ\text{F}$ )  
**Operating Temperature Range:** 0 to  $40^\circ\text{C}$  (32 to  $104^\circ\text{F}$ ) (<80% humidity)

**Storage Temperature Range:** 0 to  $60^\circ\text{C}$  (32 to  $140^\circ\text{F}$ ) (<70% humidity)  
**Response Time:** 30 to 90% absorb time 120 seconds, 90 to 30% absorb time 150 seconds  
**Dimension:** 14.2 x 160 mm (0.56 x 6.3")  
**Weight:** 50 g (1.8 oz)

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
RH-122	£20	Temperature and relative humidity tester
PTH-1XA	35	Temperature and relative humidity tester
RH-1X	26	Temperature and relative humidity pen

Comes complete with "AAA" battery and operator's manual.

**Note:** Replacement battery for RH-122 is **PH-BATT-3**, £2. Replacement battery for PTH-1XA is **HHF20-BATT**, £2.

**Ordering Example:** RH-122, compact temperature tester, **PH-BATT-3**, replacement battery, £20 + 2 = £22.



## UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA

Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)

1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany

0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England

0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)

088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)

Karviná, Czech Republic

596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters