




Self-Adhesive Patch Sensors



- ✓ 2252Ω, 5 kΩ or 10 kΩ 25°C (77°F) Elements
- ✓ Operating Range: -30 to 100°C (-22 to 212°F)
- ✓ Self Adhesive Foil Backing for Faster Response Time
- ✓ Resistant to a Variety of Chemicals and Oils
- ✓ A Range of Cable Termination Options Available
- ✓ 2 Styles Available for Flat or Curved Surfaces

**Custom Lengths,
Insulations, and
Configurations
Available**

These sensors are available in two patch styles, for either curved or flat surfaces. The integral thermistor element is mounted flush with the self-adhesive surface of the patch, which is foil backed to minimize response times.

To Order Visit omega.com/sa2f-th for Pricing and Details			
Model Number	Resistance	Interchangeability @ 0 to 70°C	Wire Length
SA2F-TH-44033-40	2252Ω @ 25°C	±0.1°C	1 m (40"), stripped leads
SA2F-TH-44034-40	5000Ω @ 25°C	±0.1°C	1 m (40"), stripped leads
SA2F-TH-44031-40	10,000Ω @ 25°C	±0.1°C	1 m (40"), stripped leads
SA2C-TH-44033-40	2252Ω @ 25°C	±0.1°C	1 m (40"), stripped leads
SA2C-TH-44034-40	5000Ω @ 25°C	±0.1°C	1 m (40"), stripped leads
SA2C-TH-44031-40	10,000Ω @ 25°C	±0.1°C	1 m (40"), stripped leads

Notes: For longer cable length, change "-40" with required length (in inches) to end of the model number for an additional cost per foot. For 1/4" jack plug, add "-PP" to the model number for an additional cost.

Ordering Examples: SA2C-TH-44033-40, thermistor patch sensor for curved surfaces, 2252Ω at 25°C, 1 m (40") of cable with stripped leads. SA2F-TH-44031-120-PP, thermistor patch sensor for flat surfaces, 10,000Ω at 25°C, 3 m (10') of cable with 1/4" jack plug.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters