

Infrared Transmitter Fiber Optic Probes 4 to 20 mA Output

OS1553 Series
\$2475
All Models



- ✓ Reaches Difficult-to-Access Locations
- ✓ Fast, Precise 10 msec Time Constant
- ✓ Ideal for Small Targets with Spot Sizes Down to 0.004" Available
- ✓ Adjustable Emissivity for High Accuracy
- ✓ Spectral Filtering Allows Use in Dirty Atmospheres
- ✓ Works with Standard Process Meters and Controllers

The OS1553 is a self-contained fiber optic infrared transmitter designed to provide a linear 4 to 20 mA output for monitoring, datalogging or controlling temperature.

The detector can be remotely mounted as far as 9 m (30') away from the fiber optic lens via the fiber optic cable, removing it from hazardous locations. Other problems that can be overcome by the OS1553's fiber optic design include: taking measurements in high energy fields; measuring very small objects or surfaces; taking measurements in "dirty" atmospheres containing water vapor, dust or smoke.

Some important factors that will determine the fiber optic assembly needed for your infrared application are: the distance from the fiber optic lens to the surface being measured; the size of the object being measured; temperature range; ambient temperature around the fiber optic cable; the length of the cable; the method of heating the surface being measured; and the atmospheric conditions between the fiber optic lens and product.

OS1553-L1-R1-4,
\$2475, shown
smaller than
actual size.



OS1553-MB mounting
bracket, included.

Specifications

Accuracy: $\pm 1.0\%$ rdg or 1.7°C ($\pm 3^\circ\text{F}$), whichever is greater

Spectral Response:

0.95 to 1.09 microns

Repeatability: $\pm 1^\circ\text{C}/\text{F}$ or less

Time Constant: 10 msec (0 to 63.2%)

Output: 4 to 20 mA linear output

Power: 20 to 40 Vdc, 100 mA
Regulated, 0.02%

Maximum Loop Resistance:

$$\frac{V_{\text{source}} - 20}{20 \text{ mA}}$$

Emissivity: 0.05 to 0.99,
adjustable in 0.01 steps

Ambient Temperature:
0 to 50°C (32 to 122°F)


Dimensions:

8.64 H x 12.07 W x 24.77 cm D
(3.40 x 4.75" x 9.75")

Weight: 1.8 kg (4 lb)

Fiber Optic Cable: Glass fiber material,
heavy-duty stainless steel jacket,
0.23" O.D., 300°F max

Probe: 25.4 diameter by
up to 279 mm long (1 by 11")



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| Model No. | Base Price | Temp Range | Spot Size @ Target Dist | Cable Length |
|----------------|------------|--|-------------------------|---------------|
| OS1553-L1-R1-4 | \$2475 | 816 to 1370°C (1500 to 2500°F) | 0.020" @ 6" | 1.2 m (4') |
| OS1553-L1-R2-4 | 2475 | 565 to 840°C (1050 to 1550°F) | 0.16" @ 3" | 1.2 m (4') |
| OS1553-L1-R3-4 | 2475 | 565 to 840°C (1050 to 1550°F) | 0.79" @ 12" | 1.2 m (4') |
| OS1553-L1-R4-4 | 2475 | 816 to 1370°C (1500 to 2500°F) | 0.50" @ 32" | 1.2 m (4') |

Consult OMEGA for information on custom OS1553 fiber optic systems to suit any application.

Accessories

| Model No. | Price | Description |
|-----------|-------|--|
| PSS-D15B | \$114 | ± 15 Vdc or 30 Vdc regulated power supply, ± 100 mA, 0.02% line and load, 115 Vac input |
| OS1553-MB | 95 | Additional mounting bracket |

Comes with probe assembly, fiber optic cable, mounting bracket, and operator's manual.
Ordering Example: OS1553-L1-R1, fiber optic sensor with 816 to 1370°C (1500 to 2500°F) range, 0.02" spot size at 6" target distance, and PSS-D15B power supply, $\$2475 + 114 = \2589 .

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters