

Food Service Infrared Thermometer

With Penetration Probe (304 Stainless Steel)



OS303
\$139



- ✓ Hazard Analysis and Critical Control Point (HACCP)
- ✓ Non-Contact Surface or Internal Temperature Measurement
- ✓ Min/Max Mode
- ✓ °C or °F Selectable
- ✓ Adjustable Emissivity
- ✓ Auto Power Off

The OS303 utilizes a Hazard Analysis and Critical Control Point (HACCP) check mode which features 3 visible LED icons to indicate whether the temperature is within FDA guidelines for frozen or hot foods. The OS303 also features a lock mode for continuous readings of up to 30 minutes for infrared surface temperatures and 4 minutes for internal readings with the stainless steel penetration probe.

Specifications

Infrared Range: -55 to 250°C (-67 to 572°F)

Infrared Accuracy: 1.8°F up to 150°F ±1.5% of reading thereafter

Infrared Resolution: 0.2°C (0.5°F)

Contact Probe Range: -55 to 330°C (-67 to 626°F)

Contact Accuracy:

Below -5°C (23°F): ±1°C (1.8°F)

-5 to 66°C (23°F to 150°F): ±1°C (0.8°F)

Above 66°C (150°F): ±1% of reading

Distance to Spot Ratio: 2.5:1

Battery Type:

2 "AAA" 1.5V batteries (included)


Dimensions:

22.1 D x 38.1 W x 190 mm L (0.87 x 1.5 x 7.48")

Weight: 0.1 kg (3.15 oz) with batteries



OS303, \$139, shown actual size.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OS303	\$139	Food service infrared thermometer with penetration probe

Comes complete with 2 "AAA" batteries and operator's manual.

Ordering Example: OS303, food service thermometer, \$139.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters