



# Dual Solid State Relays

## 25 and 40 A; Vdc Input/ Vac Output

SSRLDUAL Series  
Starts at  
**\$53**



- ✓ Two 25 or 40 A SSR's in 1 Standard Package
- ✓ Opto-Isolated 2500 VRMS

The OMEGA® SSRLDUAL Series solid-state relays are 2 totally independent AC output relays in a single standard panel mount package. They utilize OMEGA's inverse-parallel SCR output design with integral dV/dt snubber circuitry to provide protection against false triggering by limiting the rate of rise of most voltage transients to within acceptable limits. Zero volt turn-on and zero current turn-off of the load being switched substantially reduces EMI and RFI.

### General Specifications

**Operating Temperature:** -40 to 80°C (-40 to 176°F)

**Storage Temperature:** -40 to 100°C (-40 to 212°F)

**Input to Output Isolation:** 4000 Vrms

**Input/Output to Ground Isolation:** 2500 Vrms

**Input to Output Capacitance:** 8 pF (typical)

**Operating Frequency:** 47 to 63 Hz

**Housing Material:** UL 94V0 (self-extinguishing)

### Output

**Voltage Range (Vrms):** 24 to 280 Vac

**Peak Voltage (Vpk, t = 1 Minute):** 550

**Off-State Leakage (@ Max Line Voltage and Ta = 25°C):** 0.1 mArms

**Output Current (Mounted on Proper Heat Sink, See Deratings):**

DC25: 25  
DC40: 40

**Minimum Current:** 100 mArms

**Maximum 1-Cycle Surge Current (Apk, Ta = 25°C):**

DC25: 500  
DC40: 780

**Forward Voltage Drop (Vpk @ Imax, Ta = 25°C):**

DC25: 1.4  
DC40: 1.3

**I<sup>2</sup>T (60 Hz, ½ Cycle):**

DC25: 1041  
DC40: 2435

**R<sub>jb</sub> (Thermal Res. Junction to Baseplate):**

DC25: 0.6  
DC40: 0.4

**Static Off-State dv/dt (V<sub>ps</sub>, Ta = 25°C):** 500

### Input

**Input Voltage:** 4 to 15 Vdc

**Drop-Out Voltage:** 1 Vdc

**Minimum Input Current (for On-State):** 7.5 mA

**Maximum Input Current:** 34 mA

**Input Resistance:** 500 Ω




**Turn-On Time\*:** 8.33 ms

**Turn-Off Time:** 8.33 ms

\* Random SSR's turn on in less than 100 μs.



SSRLDUAL240DC25, \$53, shown smaller than actual size.



**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Model Number	Price	Description
SSRLDUAL240DC25	\$53	25 A dual SSR output
SSRLDUAL240DC40	60	40 A dual SSR output
CX136-4	3	Connector

Comes with complete operator's manual.

Ordering Example: SSRLDUAL240DC25, 25 A dual SSR output, \$53

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters